

Quick Installation Guide

Version 1.0

Universal PCI Multi-Port Communication Board











Introduction

DIGITUS I/O series, a line of Universal PCI Multi-port Serial Communication Board, is a 32-bit Plug-n-Play PCI Bus card equipped with independent high-speed standard serial interfaces. The card attaches 1 / 2 / 4 independent DB9 or DB25 serial ports on your system for industrial communication and automation applications. It is compatible with both 3.3V or 5V and 32-bit or 64-bit PCI Bus, allowing this multi-port serial card to be installed in virtually any available PC system and compatible with all major operating systems. Users do not need to manually set jumpers to configure I/O addresses and IRQ locations. The system will search the device automatically eliminating any conflicts with other cards or devices.

Features

- Fully compatible with PCI Spec. Ver2.2 / 2.1standard.
- Supports both 64-bit & 32-bit PCI Bus and 3.3V &5V connector keys.
- Expands 1 / 2 / 4 independent RS-232 serial ports in one single board. (Note)
- High speed 16C650 compatible communication controller with SUN1889 single chip hardware flow control to guarantee no data loss and best technical support.
- Each serial port has built-in 32 byte hardware FIFO.
- Data transmission speeds up to 115.2 Kbps.
- Certified by Microsoft WHQL, CE, FCC ClassB approval.
- Support Microsoft Windows, DOS, Linux, and SCO Unix major operation system.
- Ready for the Intel® and AMD® 32 and 64-bit platform system.

Package List

Please check if the following items are present and in good condition upon opening your package. Contract your vendor if any item is damaged or missing.

- RS-232 Universal PCI Multi-Port Communication Board
- Quick Installation Guide (this document)
- CD Driver
- User Manual
- Serial Cable (Note)

1 port series: Do NOT need any connection cable. 2 ports series : Do NOT need any connection cable.

4 ports series: DB37 Male to 4 ports DB9 or DB25 Male × 1

NOTE:

We provide 1, 2 or 4 ports product for users selection. The expansions COM ports and cable accessory will depend on what product you bought.

Specification

Model	Universal PCI Communication Board		
Mode of Operation	HandShaking Full-Duplex		
Controller	SUN1889 16C650 Compatible UART		
Bus Interface	64-bit & 32-bit PCI Bus / 3.3V & 5V Connector Key		
Number of Ports	1/2/4 ports with DB9 or DB25 Male Type		
Bracket	Standard 121 mm, Low Profile79.2 mm		
IRQ & IO Address	Assigned by BIOS / O.S.		
FIFO	32 byte hardware FIFO		
Baud Rate	75 ~ 115,200bps		
Data Bit	5, 6, 7, 8		
Stop bit	1, 1.5, 2		
Parity	Even, Odd, None, Mark, Space		
Flow Control	None, Xon/Xoff, HardWare		
Pin Assignment	TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND DB9M DB25M DB25M DCD 8 RxD 2 3 1 2 3 4 5 6 7 8 5 7 1 1 1 1 1 1 1 1 1		
Driver Support	Windows CE 5.0 / 3.1 / 9x / NT / 2000 / XP / 2003 / Vista / 7; Linux 2.2.x, 2.4.x, 2.6.x; DOS		
Regulatory Approvals	CE, FCC / Microsoft WHQL		
Operation Temperature 0°C ~ 60°C (32°F ~ 140°F)			

Driver Installation

In order to ensure proper operation of your PCI serial board, the driver will be in the CD bound with your product. You can specify the location (folder) as below:


Operation System		Driver Location
Windows 2000/XP/2003/Vista/7 (32	2-Bit	:\IO\PCI IO\2K & XP & 2003&Vista_32bit\
Windows XP / 2003/Vista (64-bit)		:\IO\PCI IO\XP& 2003&Vista_64 bit\
Windows 95 / 98 / Me		:\IO\PCI IO\Win9x\
Windows NT4.0		:\IO\PCI IO\WinNT\
Windows 3.1 / DOS		:\IO\PCI IO\DOS\PCIDOS.exe
Windows CE.NET		:\IO\PCI IO\WinCE\
Linux 2.4.x, 2.6.x		:\IO\PCI IO\Linux\
User Manual		:\IO\PCI IO\Manual\Serial.pdf

X You can find the detail of the installation steps in the user manual.

Hardware Verity

Please launch the "Device Manager" to verity hardware installation correctly.

Start > Controller Panel > System > Device Manager




*The number of COM ports will depend on what products you bought.

Port Setting

After installing PCI serial board successfully, you can modify the setting for each serial port in device manager.

1. Right click your mouse on the COM port, and select "Properties".



- 2. Select "Port Setting" page to modify COM port setting.
- 3. Select "Advanced" icon, you can modify COM port number and FIFO.

